



Halogen reflector

13865 75W G5.3/4.8 12V 1CT/10X5F

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system


Product data

General Information	
Cap-Base	G5.3 [G5.3]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	35 hour(s)
Light Technical	
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	75 W
Voltage (Nom)	12 V
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Reflector Finish	Smooth
Bulb Shape	R35 [R 35mm]
Product Data	
Order product name	13865 75W G5.3/4.8 12V 1CT/10X5F
Full product name	13865 75W G5.3/4.8 12V 1CT/10X5F
Full product code	871869668102200
Order code	924060017101
Material Nr. (12NC)	924060017101
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696681022
Numerator - Packs per outer box	50
EAN/UPC - Case	8718696681046

Halogen reflector

Dimensional drawing



Product	D (max)	C (max)
13865 75W G5.3/4.8 12V 1CT/10X5F	35 mm	35.5 mm

