



Low Voltage Capsules

LV Capsule BC10W/T3/LAND/TP/12VCAPSULE 2PK

Functional light with substantial energy savings. Philips Halogen Low Voltage Capsules provide sparkling, white light. These lamps offer an average rated life of 2000 hours making them perfect for undercabinet or task lighting.

Warnings and Safety

• This lamp is pressurized and could shatter, so to avoid any injury and to avoid exposure to ultraviolet radiation, use only in fixtures that provide a protective shield of tempered glass.

Product data


General Information			
Cap-Base	G4 [G4]		
Operating Position	UNIVERSAL [Any or Universal (U)]		
Nominal lifetime	2,000,000 hour(s)		
Rated Lifetime (Hours)	2,000 hour(s)		
Lighting Technology	Halogen		
Light Technical			
Luminous Flux	100 lm		
Correlated Color Temperature (Non	n) 3000 K		
Luminous Efficacy (rated) (Nom)	10 lm/W		
Color rendering index (CRI)	100		
Operating and Electrical			
Power Consumption	10 W		
Lamp Current (Nom)	0.83 A		
Starting Time (Nom)	0.0 s		
Voltage (Nom)	12 V		

Malka an (Nama)	12.1/
Voltage (Nom)	12 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T9 [T 9mm (T9)]
Product Data	
Order product name	BC10W/T3/LAND/TP/12VCAPSULE 2PK
Full product name	LV Capsule BC10W/T3/LAND/TP/12VCAPSULE
	2PK
Order code	417212
Material Nr. (12NC)	924062117102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677417215
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677417210

Datasheet, 2023, September 26 data subject to change

Low Voltage Capsules

Dimensional drawing



Product	D (max)	L	C (max)
BC10W/T3/LAND/TP/12VCAPSULE 2PK	7/16 inch	7/8 inch	1-5/16 inch

