



Low Voltage Capsules

LV Capsule BC20W/T3/12V/CAPSULE 12/1

Functional light with substantial energy savings. Philips Halogen Low Voltage Capsules provide sparkling, white light. These lamps offer an average rated life of 2000 hours making them perfect for undercabinet or task lighting.

Warnings and Safety

- This lamp is pressurized and could shatter, so to avoid any injury and to avoid exposure to ultraviolet radiation, use only in fixtures that provide a protective shield of tempered glass.

Product data

General Information	
Cap-Base	G4 [G4]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2.000 hour(s)
Switching Cycle	8.000
Rated Lifetime (Hours)	2.000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	255 lm
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	20 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T9 [T 9mm (T9)]
Product Data	
Order product name	BC20W/T3/12V/CAPSULE 12/1
Full product name	LV Capsule BC20W/T3/12V/CAPSULE 12/1
Order code	415661
Material Nr. (12NC)	924062217122
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677415662
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677415667

Low Voltage Capsules

Dimensional drawing



Product	D (max)	L	C (max)
BC20W/T3/12V/CAPSULE 12/1	10 mm	22 mm	33 mm

