



Low Voltage Capsules

LV Capsule BC20W/T3/LAND/TP/12VCAPSULE 2PK

Functional light with substantial energy savings. Philips Halogen Low Voltage Capsules provide sparkling, white light. These lamps offer an average rated life of 2000 hours making them perfect for undercabinet or task lighting.

Warnings and Safety


- This lamp is pressurized and could shatter, so to avoid any injury and to avoid exposure to ultraviolet radiation, use only in fixtures that provide a protective shield of tempered glass.

Product data

General Information		Controls and Dimming	
Cap-Base	G4 [G4]	Dimmable	Yes
Operating Position	UNIVERSAL [Any or Universal (U)]		
Nominal lifetime	2,000,000 hour(s)	Mechanical and Housing	
Switching Cycle	8,000	Bulb Finish	Clear
Rated Lifetime (Hours)	2,000 hour(s)	Bulb Shape	T9 [T 9mm (T9)]
Lighting Technology	Halogen		
		Product Data	
Light Technical		Order product name	BC20W/T3/LAND/TP/12VCAPSULE 2PK
Luminous Flux	255 lm	Full product name	LV Capsule BC20W/T3/LAND/TP/12VCAPSULE 2PK
Correlated Color Temperature (Nom)	3000 K	Order code	417204
Color rendering index (CRI)	100	Material Nr. (12NC)	924062217123
		Numerator - Quantity Per Pack	1
Operating and Electrical		EAN/UPC - Product/Case	046677417208
Power Consumption	20 W	Numerator - Packs per outer box	12
Starting Time (Nom)	0.0 s	EAN/UPC - Case	50046677417203
Voltage (Nom)	12 V		
Voltage (Nom)	12 V		

Low Voltage Capsules

Dimensional drawing



Product	D (max)	L	C (max)
BC20W/T3/LAND/TP/12VCAPSULE 2PK	7/16 inch	7/8 inch	1-5/16 inch

