



Halogen non-reflector

12345SL 20W G4 12V 1CT/24

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.

Product data

General Information	
Cap-Base	G4
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	100 hour(s)

Light Technical	
Correlated Color Temperature (Nom)	3100 K
Color rendering index (CRI)	100


Operating and Electrical	
Power Consumption	20 W
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	12345SL 12V 20W G4 PH
Full product name	12345SL 20W G4 12V 1CT/24
Full product code	871869669023900
Order code	324046
Material Nr. (12NC)	924068417104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696690239
Numerator - Packs per outer box	24
EAN/UPC - Case	8718696690246

Halogen non-reflector

Dimensional drawing



Product	D (max)	L (min)	L (max)	L	C	P (max)	P	P (min)
12345SL 12V	3/8 inch	3/4 inch	13/16	13/16	1-3/16	1/16 inch	1/16	1/16
20W G4 PH			inch	inch	inch		inch	inch

