



# Halogen non-reflector

## 12345SL 12V 20W G4 PH

Halogen non-reflector lamps offer high-quality light and are easy to install, replace and operate. All halogen non-reflector lamps incorporate a distortion-free quartz bulb and a precise positioning of the mounted filament. These ensure optimal beam performance and consistent, high light output. A wide range of wattages is available for a broad variety of applications, including projection systems. In addition you get all the proven advantages of halogen technology such as a full spectrum and a color rendering index (CRI) of 100 – the same as natural light and the best that it can be. Halogen lamps also create a comfortable warm white light, and they maintain their lumen output, with almost no reduction, throughout their lifetime.


### Product data

General Information	
Cap-Base	G4
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	100 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3100 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	20 W
Voltage (Nom)	12 V
Voltage (Nom)	12 V
Mechanical and Housing	
Bulb Material	Quartz-UV Open

Product Data	
Order product name	12345SL 12V 20W G4 PH
Full product name	12345SL 12V 20W G4 PH
Full product code	871869669023900
Order code	924068417104
Material Nr. (12NC)	924068417104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696690239
Numerator - Packs per outer box	24
EAN/UPC - Case	8718696690246

# Halogen non-reflector

## Dimensional drawing



Product	D (max)	L (min)	L (max)	L	C	P (max)	P	P (min)
12345SL 12V	8.5 mm	19.25	19.75 mm	19.5	30	0.75 mm	0.7	0.65 mm
20W G4 PH		mm		mm	mm		mm	

