



Appliance Refrigerator Tubular

APPL 15W E14 230-240V T25 CL RF 1CT

Tubular lamp with clear glass bulb

Product data

General Information	
Cap-Base	E14
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	110 lm
Correlated Color Temperature (Nom)	2700 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	15.0 W
Lamp Current (Nom)	0.06 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230-240 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing		
Bulb Finish	Clear	
Bulb Shape	T25	
Approval and Application		
Energy Consumption kWh/1000 h	15 kWh	
Product Data		
Order product name	Appl 15W E14 230-240V T25 CL RF 1CT	
Full product name	APPL 15W E14 230-240V T25 CL RF 1CT	
Full product code	871150003851750	
Order code	03851750	
Material Nr. (12NC)	924197744440	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8711500038517	
Numerator - Packs per outer box	100	
EAN/UPC - Case	8711500250827	

Appliance Refrigerator Tubular

Dimensional drawing

Product	D (max)	C (max)
Appl 15W E14 230-240V T25 CL RF 1CT	25 mm	57 mm





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, August 28 - data subject to change