

PHILIPS

Lighting



Appliance Refrigerator Tubular

APPL 15W E14 230-240V T25 CL RF 2BL/10

Tubular lamp with clear glass bulb

Product data

General Information

Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 h
Switching Cycle	4,000
Rated Lifetime (Hours)	1,000 h
Lighting Technology	Incandescent

Light Technical

Luminous Flux	110 lm
Correlated Colour Temperature	2700 K
Colour rendering index (CRI)	100

Operating and Electrical

Power Consumption	15.0 W
Lamp current (nom.)	0.06 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	230-240 V

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Lamp Finish	Clear
Bulb shape	T25 [T 25 mm]

Approval and Application

Energy consumption kWh/1,000 hours	15 kWh
------------------------------------	--------

Product Data

Order product name	Appl 15W E14 230-240V T25 CL RF 2BL/10
Full product name	APPL 15W E14 230-240V T25 CL RF 2BL/10
Full EOC	871150025024725
Order code	25024725
Material no. (12 NC)	924197744452
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500250247
Numerator – packs per outer box	10
EAN/UPC - Case	8711500259837

Appliance Refrigerator Tubular

Dimensional drawing

Product	D (max)	C (max)
Appl 15W E14 230-240V T25 CL RF 2BL/10	25 mm	57 mm

