



InfraRed Industrial Heat Incandescent

IR R115 245W 220V Clear 1CT/4


The Philips infrared incandescent reflector lamps are designed to work in the toughest environment such as farm, bathroom or kitchen and their nearest surrounding. They have a reinforced construction thanks to hard glass use. Their compact form and universal cap base allow them to be used with any suitable equipment. A very good method of generating warmth is by using heat lamps. The Philips infrared lamps provide direct, draught-free warmth to the animals, but also food. These benefits have made farmers and cooks around the world choose Philips infrared lamps, because they are the sturdiest, most efficient lamps available for these applications.

Product data

General Information		Bulb Shape	
Cap-Base	E27/51 [E27/51]	R115 [R 115mm]	
Nominal lifetime	5,000 hour(s)	Product Data	
Rated Lifetime (Hours)	5,000 hour(s)	Full product code	692341077160200
Lighting Technology	Incandescent	Order product name	IR R115 245W 220V Clear 1CT/4
Operating and Electrical		Order code	924578542902
Power Consumption	245.0 W	Numerator - Quantity Per Pack	1
Warm-up time to 60% light	Instant full light s	Numerator - Packs per outer box	4
Voltage (Nom)	220 V	Material Nr. (12NC)	924578542902
Voltage (Nom)	220 V	Full product name	IR R115 245W 220V Clear 1CT/4
Mechanical and Housing		EAN/UPC - Case	6923410771619
Bulb Finish	Clear	EAN/UPC - Product/Case	6923410771602

InfraRed Industrial Heat Incandescent

Dimensional drawing



Product	D	C (max)
IR R115 245W 220V Clear 1CT/4	115 mm	162 mm

