



# Plusline ES Small

## Plusline 118mm 2y 120W R7s 230V 1BB

Mains-voltage halogen linear lamp with superior quality and reliability. Offers very long lifetime and crisp halogen light. Ideal solution for decorative luminaires and for security or task lighting floodlights.


### Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	2,220 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	18.5 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	120.0 W
Lamp Current (Nom)	0.52 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11 [T 11mm]
Approval and Application	
Energy Consumption kWh/1000 h	120 kWh
Product Data	
Order product name	Plusline 118mm 2y 120W R7s 230V 1BB
Full product name	Plusline 118mm 2y 120W R7s 230V 1BB
Full product code	872790085216500
Order code	85216500
Material Nr. (12NC)	924587444210
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900852165
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900852189

## Plusline ES Small

### Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline 118mm 2y 120W R7s 230V 1BB	11 mm	115.8 mm	114.2 mm	112.6 mm	118 mm

