



Plusline ES Small

Halogen 118MM 2Y 160W R7S 230V 1BC/10

Mains-voltage halogen linear lamp with superior quality and reliability. Offers very long lifetime and crisp halogen light. Ideal solution for decorative luminaires and for security or task lighting floodlights.

Product data

General Information	
Cap-Base	R7s
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	3,100 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	19.4 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	160.0 W
Lamp Current (Nom)	0.70 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11

Approval and Application	
Energy Consumption kWh/1000 h	160 kWh

Product Data	
Order product name	Halogen 118MM 2Y 160W R7S 230V 1BC/10
Full product name	Halogen 118MM 2Y 160W R7S 230V 1BC/10
Full product code	872790092088800
Order code	924587544220
Material Nr. (12NC)	924587544220
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900920888
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900920895

Plusline ES Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Halogen 118MM 2Y 160W R7S 230V 1BC/10	11 mm	115.8 mm	114.2 mm	112.6 mm	118 mm

