



Double Ended Linear

Double Ended Linear 300T3Q/CL 120V 12PK

High-quality white light with superior lumen performance Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

| General Information | |
|---------------------------------|------------------------|
| Base | R7S [R7s] |
| Operating Position | Universal [Universal] |
| Nominal Lifetime (Nom) | 2000 h |
| Light Technical | |
| Initial lumen (Nom) | 5200 lm |
| Luminous Efficacy (rated) (Nom) | 17.3 lm/W |
| Operating and Electrical | |
| Power (Rated) (Nom) | 300 W |
| Lamp Current (Nom) | 2.50 A |
| Starting Time (Nom) | 0.0 s |
| Voltage (Nom) | 120 V |
| Mechanical and Housing | |
| Bulb Finish | Clear |

| Approval and Application | |
|---------------------------------|---|
| Energy Efficiency Label (EEL) | E |
| Luminaire Design Requirements | |
| Bulb Temperature (Max) | 900 °C |
| Pinch Temperature (Max) | 350 °C |
| Product Data | |
| Order product name | Double Ended Linear 300T3Q/CL 120V 12PK |
| EAN/UPC - Product | 046677392826 |
| Order code | 392829 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 12 |
| Material Nr. (12NC) | 924735234593 |
| Net Weight (Piece) | 0.010 kg |

Double Ended Linear

Dimensional drawing



| Product | D (max) | B (max) | B | B (min) | C (max) |
|--|---------|----------|----------|----------|----------|
| Double Ended Linear 300T3Q/CL 120V 12PK | 12 mm | 115.8 mm | 114.2 mm | 112.6 mm | 117.6 mm |

DESmall 300W R7s 120V

