



Double Ended Linear

PLUS PRO S 500W R7s 120V 1CT/12

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	9,500 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	19.0 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	500 W
Lamp Current (Nom)	4.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V
Voltage (Nom)	120 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]

Product Data	
Order product name	PLUS PRO S 500W R7s 120V 1CT/12
Full product name	PLUS PRO S 500W R7s 120V 1CT/12
Order code	924735334593
Material Nr. (12NC)	924735334593
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677100100
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677100105

Double Ended Linear

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
PLUS PRO S 500W R7s 120V 1CT/12	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

