



Plusline Small

Plusline S 300W R7s 230V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light


Product data

Informasi Umum	
Tutup-Dasar	R7s
Posisi Pengoperasian	UNIVERSAL [Setiap atau Universal (U)]
Nominal masa pakai	2.000 jam
Nilai Masa Pakai (Jam)	2.000 jam
Teknologi Pencahayaan	Halogen
Teknis Lampu	
Flux Cahaya	5.114 lm
Suhu Warna Terkorelasi (Nom)	2900 K
Daya Penerangan (terukur) (Nom)	17 lm/W
Indeks renderasi warna (CRI)	100
Pengoperasian dan Kelistrikan	
Konsumsi Daya	300 W
Arus Lampu (Nom)	1,3 A
Waktu Mulai (Nom)	0,0 s
Tegangan (Nom)	230 V
Tegangan (Nom)	230 V

Kontrol dan Peredupan	
Dapat diredupkan	Ya
Mekanis dan Housing	
Lapisan bohlam	Bening
Bentuk Bohlam	T3 [T 12mm (T3)]
Data Produk	
Nama produk pesanan	Plusline S 300W R7s 230V 1CT/10X10F
Nama lengkap produk	Plusline S 300W R7s 230V 1CT/10X10F
Kode produk lengkap	872790080895700
Kode urutan	924735444201
No. Material (12NC)	924735444201
Kode urutan lokal	PLUSLINE300W23
Numerator - Jumlah Per Pak	1
EAN/UPC - Produk/Kantung	8727900808957
Numerator - Pak per kotak bagian luar	100
EAN/UPC - Kantung	8727900808964

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline S 300W R7s 230V 1CT/ 10X10F	12 mm	115,8 mm	114,2 mm	112,6 mm	117,6 mm

