



Plusline Small

Plusline S 300W R7s 230V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light

Product data

General Information	
Cap-Base	R7S [R7s]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

Light Technical	
Luminous Flux	5,114 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	17 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	300 W
Lamp Current (Nom)	1.3 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Voltage (Nom)	230 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T3 [T 12mm (T3)]

Product Data	
Order product name	Plusline S 300W R7s 230V 1CT/10X10F
Full product name	Plusline S 300W R7s 230V 1CT/10X10F
Full product code	692234192040000
Order code	924735444289
Material Nr. (12NC)	924735444289
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341920400
Numerator - Packs per outer box	100
EAN/UPC - Case	6922341920417

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline S 300W R7s 230V 1CT/ 10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

