



Plusline Small

Plusline S 500W R7s 240V 1CT/10X10F

Mains-voltage linear lamp giving white halogen light

Product data

General Information	
Cap base	R7S [R7s]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Light Technical	
Luminous flux (nom.)	9660 lm
Correlated Colour Temperature (Nom)	2900 K
Luminous efficacy (rated) (nom.)	19.3 lm/W
Color rendering index (nom.)	100
Operating and Electrical	
Power (Rated) (Nom)	500 W
Lamp current (nom.)	2.08 A
Starting time (nom.)	0.0 s
Voltage (Nom)	240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Clear

Approval and Application	
Energy efficiency label (EEL)	D
Luminaire Design Requirements	
Bulb temperature (max.)	900 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	872790080905300
Order product name	Plusline S 500W R7s 240V 1CT/10X10F
EAN/UPC – product	8727900809053
Order code	80905300
Numerator – quantity per pack	1
Numerator – packs per outer box	100
Material no. (12NC)	924735545579
Net weight (piece)	0.010 kg
ILCOS Code	HDG//RS-500-240-R7s-114,2

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Plusline S 500W R7s 240V 1CT/10X10F	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

DESmall 500W R7s 240V T3 CL

