



# PAR56 and PAR64

## PAR64 1000W 240V MFL

These self-contained spotlights are ideal for intensifying the visual experience in all kinds of clubs, that is because their accurate beam control picks out even the smallest of details even over long distances. This beam control makes the PAR 56 and PAR 64 excellent for long-range light projections. In addition, the universal burning feature provides complete flexibility of luminaires angle and position, while the front glass of the PAR56 provides thermal and physical protection. The result? Complete creative freedom to achieve the desired effect. Immediate re-strike also ensures instant resumption of entertainment after any power interruption.


### Product data

| General Information                |                                  |
|------------------------------------|----------------------------------|
| Cap-Base                           | GX16D [GX16d]                    |
| Operating Position                 | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime                   | 300 hour(s)                      |
| Light Technical                    |                                  |
| Beam Angle (Nom)                   | 23 degree(s)                     |
| Correlated Color Temperature (Nom) | 3200 K                           |
| Operating and Electrical           |                                  |
| Power Consumption                  | 1,000 W                          |
| Voltage (Nom)                      | 240 V                            |
| Voltage (Nom)                      | 240 V                            |
| Controls and Dimming               |                                  |
| Dimmable                           | Yes                              |

| Mechanical and Housing          |                         |
|---------------------------------|-------------------------|
| Bulb Shape                      | PAR64 [PAR 8inch/200mm] |
| Product Data                    |                         |
| Order product name              | PAR64 1000W 240V MFL    |
| Full product name               | PAR64 1000W 240V MFL    |
| Full product code               | 871150044076110         |
| Order code                      | 924783445504            |
| Material Nr. (12NC)             | 924783445504            |
| Numerator - Quantity Per Pack   | 1                       |
| EAN/UPC - Product/Case          | 8711500440761           |
| Numerator - Packs per outer box | 6                       |
| EAN/UPC - Case                  | 8711500440778           |

# PAR56 and PAR64

## Dimensional drawing



| Product              | D (max) | C (max) |
|----------------------|---------|---------|
| PAR64 1000W 240V MFL | 204 mm  | 150 mm  |

