

PAR56 and PAR64

PAR56 300W 230V MFL

These self-contained spotlights are ideal for intensifying the visual experience in all kinds of clubs, that is because their accurate beam control picks out even the smallest of details even over long distances. This beam control makes the PAR 56 and PAR 64 excellent for long-range light projections. In addition, the universal burning feature provides complete flexibility of luminaires angle and position, while the front glass of the PAR56 provides thermal and physical protection. The result? Complete creative freedom to achieve the desired effect. Immediate re-strike also ensures instant resumption of entertainment after any power interruption.

Product data

General Information	
Cap-Base	GX16D [GX16d]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)

Light Technical	
Beam Angle (Nom)	20 degree(s)
Correlated Color Temperature (Nom)	3000 K

Operating and Electrical	
Power Consumption	300 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	PAR56 [PAR 7inch/180mm]

Product Data	
Order product name	PAR56 300W 230V MFL
Full product name	PAR56 300W 230V MFL
Full product code	871150044188110
Order code	924783644204
Material Nr. (12NC)	924783644204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500441881
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500441898

PAR56 and PAR64

Dimensional drawing



Product	D (max)	C (max)
PAR56 300W 230V MFL	178 mm	127 mm

© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.