



# Halogen reflector

## JCR 15V 150W H5 24 PACK

Quartz halogen lamps with integral reflector which serves as an efficient mirror condenser system

### Product data

General Information	
Cap-Base	GZ6.35 [GZ6.35]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Life to 50% Failures (Nom)	500 hour(s)
Light Technical	
Correlated Color Temperature (Nom)	3100 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	150 W
Voltage (Nom)	15 V
Voltage (Nom)	15 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Material	Quartz-UV Open
Reflector Finish	Smooth
Bulb Shape	R50 [R 50mm]
Product Data	
Order product name	JCR 15V 150W H5 24 PACK
Full product name	JCR 15V 150W H5 24 PACK
Full product code	871150041329130
Order code	924793618594
Material Nr. (12NC)	924793618594
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500413291
Numerator - Packs per outer box	24
EAN/UPC - Case	8711500413307

# Halogen reflector

## Dimensional drawing



Product	D (max)	C (max)
JCR 15V 150W H5 24 PACK	50 mm	43 mm

