



Essential LV MR11

Ess MR11 20W GU4 12V 30D 1CT/10X5F

The Essential LV MR11 is part of the Philips "Value for Money" ranges. It is a good choice for professional end-users looking for high-quality accent light to create contrast in shops, hotels and restaurants


Product data

General Information	
Cap-Base	GU4 [GU4]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Beam Angle (Nom)	30 degree(s)
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	20 W
Lamp Current (Nom)	1.67 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	12 V
Voltage (Nom)	12 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	MR11 [1.375inch/35mm]
Product Data	
Order product name	Ess MR11 20W GU4 12V 30D 1CT/10X5F
Full product name	Ess MR11 20W GU4 12V 30D 1CT/10X5F
Full product code	692341076338600
Order code	924884017160
Material Nr. (12NC)	924884017160
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923410763386
Numerator - Packs per outer box	50
EAN/UPC - Case	6923410764314

Essential LV MR11

Dimensional drawing



Product	D (max)	C (max)
Ess MR11 20W GU4 12V 30D 1CT/10X5F	35.3 mm	40 mm

