



Double Ended Linear

Double Ended Linear BC250T3Q/CL 120V 12/1PK


High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

General Information		Cap-Base Information	
Base	R7S [R7s]	Cap-Base Information	na [-]
Nominal Lifetime (Nom)	2000 h	Approval and Application	
Light Technical		Energy Efficiency Label (EEL)	E
Initial lumen (Nom)	4000 lm	Luminaire Design Requirements	
Correlated Color Temperature (Nom)	2900 K	Bulb Temperature (Max)	900 °C
Luminous Efficacy (rated) (Nom)	16 lm/W	Pinch Temperature (Max)	350 °C
Color Rendering Index (Nom)	100	Product Data	
Operating and Electrical		Order product name	Double Ended Linear BC250T3Q/CL 120V 12/1PK
Power (Rated) (Nom)	250 W	EAN/UPC - Product	046677415624
Lamp Current (Nom)	2.08 A	Order code	415620
Starting Time (Nom)	0.0 s	Numerator - Quantity Per Pack	1
Voltage (Nom)	120 V	Numerator - Packs per outer box	12
Controls and Dimming		Material Nr. (12NC)	924884736301
Dimmable	Yes	Net Weight (Piece)	0.006 kg
Mechanical and Housing			
Bulb Finish	Clear		

Double Ended Linear

Dimensional drawing



Product

Double Ended Linear BC250T3Q/CL 120V 12/1PK

DEComp 250W R7s 120V T3 CL

