



Reflector Flood

45R20 130V 12/1

Philips Family of Specialty Incandescents provide the perfect light for dramatic accents and display lighting as well as general lighting in a variety of applications. These flood lamps produce homogeneous beams of high intensity for general illumination.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	380 lm
Operating and Electrical	
Power Consumption	45 W
Voltage (Nom)	130 V
Voltage (Nom)	130 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	R20 [R 63mm]
Product Data	
Order product name	45R20 130V 12/1
Full product name	45R20 130V 12/1
Order code	203224
Material Nr. (12NC)	925154436103
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677203221
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677203226

Reflector Flood

Dimensional drawing



Product	C (max)
45R20 130V 12/1	3.94 inch

