



# Switchboard

## 15T6 140-150V 24/1

Philips Family of Specialty Incandescents provide the perfect light for display lighting as well as general lighting in a variety of applications. From tubular shapes and appliance bulbs, to colored lamps made specifically for holiday, party or special effects lighting, this family of lamps has everything needed for professional and consumer applications.

### Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	100 lm
Operating and Electrical	
Power Consumption	15 W
Voltage (Nom)	140-150 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	T-6
Product Data	
Order product name	15T6 140-150V 24/1
Full product name	15T6 140-150V 24/1
Order code	925161758601
Material Nr. (12NC)	925161758601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677248154
Numerator - Packs per outer box	24
EAN/UPC - Case	50046677248159

# Switchboard

## Dimensional drawing

### Product

15T6 140-150V 24/1

