



# DuraMax Deco Globe

## 60G40/CL/LL 120V 6/1 TP

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Duramax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	3,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	665 lm
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	G40
Product Data	
Order product name	60G40/CL/LL 120V 6/1 TP
Full product name	60G40/CL/LL 120V 6/1 TP
Order code	168526
Material Nr. (12NC)	925178736304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677168520
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677168525

## DuraMax Deco Globe

### Dimensional drawing



#### Product

60G40/CL/LL 120V 6/1 TP

