



DuraMax Deco Globe

25G25/CL/LL 120V 12/1 TP

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Duramax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	Long Life
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	235 lm
Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	G25
Product Data	
Order product name	25G25/CL/LL 120V 12/1 TP
Full product name	25G25/CL/LL 120V 12/1 TP
Order code	925186636323
Material Nr. (12NC)	925186636323
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677168872
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677168877

DuraMax Deco Globe

Dimensional drawing

Product

25G25/CL/LL 120V 12/1 TP

