



# Standard A-shape clear

## GLS 100W/230V A55 B22CL 1SL/196+4-Ujjwal

Conventional pear-shaped incandescent lamps

### Product data

General Information	
Cap-Base	B22 [ B22]
Operating Position	UNIVERSAL [ Universal]
Nominal Lifetime (Nom)	1000 h

Light Technical	
Luminous Flux (Nom)	1350 lm
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	100 W
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear


Approval and Application	
Energy Efficiency Label (EEL)	E

Product Data	
Full product code	871829167844100
Order product name	GLS 100W/230V A55 B22CL 1SL/196+4-Ujjwal
EAN/UPC - Product	8718291678441
Order code	925209344231
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	196
Material Nr. (12NC)	925209344231
Net Weight (Piece)	28.000 g

## Standard A-shape clear

### Dimensional drawing



Product	D	C (max)
GLS 100W/230V A55 B22CL 1SL/196+4-Ujjwal	60 mm	107 mm

STD 100W B22 230V A60 Clear

