



Standard A-shape clear

GLS 60W/230V A55 B22 CL 1SL/196+4-Ujjwal

Conventional pear-shaped incandescent lamps


Product data

General Information	
Cap-Base	B22 [B22]
Nominal Lifetime (Nom)	1000 h
Light Technical	
Luminous Flux (Nom)	710 lm
Operating and Electrical	
Power (Rated) (Nom)	60 W
Voltage (Nom)	230 V
Mechanical and Housing	
Bulb Finish	Clear

Product Data	
Full product code	871829167842700
Order product name	GLS 60W/230V A55 B22 CL 1SL/196+4-Ujjwal
EAN/UPC - Product	8718291678427
Order code	925220044231
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	196
Material Nr. (12NC)	925220044231
Net Weight (Piece)	28.000 g

Standard A-shape clear

Dimensional drawing



Product	D	C (max)
GLS 60W/230V A55 B22 CL 1SL/196+4-Ujjwal	60 mm	106 mm

STD 60W B22 230V A60 CL

