



Standard A-shape clear

GLS 60W/230V A55 B22 CL 1SL/196+4-Ujjwal

Conventional pear-shaped incandescent lamps


Product data

General Information	
Cap-Base	B22 [B22]
Nominal lifetime	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	710 lm
Operating and Electrical	
Power Consumption	60 W
Voltage (Nom)	230 V
Voltage (Nom)	230 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	A55 [A 55mm]
Product Data	
Order product name	GLS 60W/230V A55 B22 CL 1SL/196+4-Ujjwal
Full product name	GLS 60W/230V A55 B22 CL 1SL/196+4-Ujjwal
Full product code	871829167842700
Order code	925220044231
Material Nr. (12NC)	925220044231
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291678427
Numerator - Packs per outer box	196
EAN/UPC - Case	8718699626587

Standard A-shape clear

Dimensional drawing



Product	D	C (max)
GLS 60W/230V A55 B22 CL 1SL/196+4-Ujjwal	60 mm	106 mm

