



DuraMax Deco Globe

40G25/W/LL 120V 4/3

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Duramax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.

Product data

General Information	
Base	E26 [Single Contact Medium Screw]
Operating Position	Universal [Universal]
Main Application	Vanity
Gas Filling	GAS
Light Technical	
Initial lumen (Nom)	370 lm
Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	White


Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	CC6 [Straight]
Product Data	
Order product name	40G25/W/LL 120V 4/3
EAN/UPC - Product	50046677169041
Order code	169045
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	925244036358
Net Weight (Piece)	39.000 g

DuraMax Deco Globe

Dimensional drawing

Product

40G25/W/LL 120V 4/3



40W E26 120V G25 WH

