



# **DuraMax Deco Globe**

## 40G25/CL/LL 120V 12/1 TP

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Duramax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.

#### **Product data**

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Rated Lifetime (Hours)	1,500 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	410 lm
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear
	-

Bulb Shape	G25 (G25)
Product Data	
Order product name	40G25/CL/LL 120V 12/1 TP
Full product name	40G25/CL/LL 120V 12/1 TP
Order code	167478
Material Nr. (12NC)	925244136345
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677167479
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677167474


Datasheet, 2023, April 17 data subject to change

## **DuraMax Deco Globe**

### Dimensional drawing

#### Product

40G25/CL/LL 120V 12/1 TP





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.