



# DuraMax Deco Globe

## BC25G16-1/2C/CL/LL 120V 6/2

Philips DuraMax® Long Life Deco Globe Bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Duramax deco globe bulbs are available in a wide assortment of shapes, sizes and wattages. Clear globes add decorative sparkle, white globes emit soft white light and half-chrome provides decorative sparkle and reduced glare.


### Product data

General Information	
Cap-Base	E12 [Candelabra Screw]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	200 lm
Operating and Electrical	
Power Consumption	25 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	G16.5 [G16.5]
Product Data	
Order product name	BC25G16-1/2C/CL/LL 120V
Full product name	BC25G16-1/2C/CL/LL 120V 6/2
Order code	168450
Material Nr. (12NC)	925244536303
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677168452
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677168457

## DuraMax Deco Globe

### Dimensional drawing



#### Product

BC25G16-1/2C/CL/LL 120V

