



DuraMax Deco Flame

BC40F15/CL/LL 120V 6/2 TP

Philips DuraMax® Long Life Decorative Flame bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative flame bulbs are available in a variety of wattages with clear, white, amber and iridescent finishes. The clear bulbs provide decorative sparkle, white bulbs provide a soft white glow, while the iridescent and amber light bulbs add a dash of shimmer and color. In their own unique ways, the different decorative flame bulbs add a pleasant touch to home decor and outdoor post lights.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	S90 [Standing +/-90D or Base Down (BDH)]
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	385 lm
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	120 V
Voltage (Nom)	120 V
Mechanical and Housing	
Bulb Finish	Clear
	-

Bulb Shape	F15 (F15)
Product Data	
Order product name	BC40F15/CL/LL 120V 6/2 TP
Full product name	BC40F15/CL/LL 120V 6/2 TP
Order code	168351
Material Nr. (12NC)	925259736309
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677168353
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677168358


Datasheet, 2023, April 30 data subject to change

DuraMax Deco Flame

Dimensional drawing

Product

BC40F15/CL/LL 120V 6/2 TP





© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.