



DuraMax Deco Blunt Tip

BC40B10-1/2C/CL/LL 120V 6/2TP

Philips DuraMax® Long Life Decorative blunt tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative blunt tip bulbs are available in a variety of shapes, sizes and wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

Product data

General Information	
Base	E12 [Candelabra Screw]
Operating Position	Base Down +/- 90 D [Base Down +/- 90 D]
Main Application	Decorative
Gas Filling	GAS

Light Technical	
Initial lumen (Nom)	300 lm

Operating and Electrical	
Power (Rated) (Nom)	40 W
Voltage (Nom)	120 V

Mechanical and Housing	
Bulb Finish	Clear

Cap-Base Information	Aluminium [Aluminium Cap]
Filament Shape	C-7A [Ring]

Product Data	
Order product name	BC40B10-1/2C/CL/LL 120V 6/2TP
EAN/UPC - Product	50046677168259
Order code	168252
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	925288536307
Net Weight (Piece)	0.012 kg

DuraMax Deco Blunt Tip

Dimensional drawing

Product

BC40B10-1/2C/CL/LL 120V 6/2TP

40W E12 120V B10 1/2 CL

