



DuraMax Deco Blunt Tip

BC40B10-1/2C/CL/LL 120V 6/2TP

Philips DuraMax® Long Life Decorative blunt tip bulbs reduce the hassle of replacing light bulbs every few months, since all DuraMax products last longer than standard incandescent light bulbs. Philips Duramax decorative blunt tip bulbs are available in a variety of shapes, sizes and wattages with clear and frost finishes. The clear bulbs provide decorative sparkle, while the frost bulbs add a soft glow to add a pleasant touch to home decor.

Product data

| General Information | | Bulb Shape | |
|---------------------------------|--|---------------------------------|-------------------------------|
| Cap-Base | E12 [Candelabra Screw] | Bulb Shape | B10 1/2 |
| Operating Position | S90 [Standing +/-90D or Base Down (BDH)] | Product Data | |
| Rated Lifetime (Hours) | 2,000 hour(s) | Order product name | BC40B10-1/2C/CL/LL 120V 6/2TP |
| Lighting Technology | Incandescent | Full product name | BC40B10-1/2C/CL/LL 120V 6/2TP |
| Light Technical | | Order code | 925288536307 |
| Luminous Flux | 300 lm | Material Nr. (12NC) | 925288536307 |
| Operating and Electrical | | Numerator - Quantity Per Pack | 1 |
| Power Consumption | 40 W | EAN/UPC - Product/Case | 046677168254 |
| Voltage (Nom) | 120 V | Numerator - Packs per outer box | 6 |
| Voltage (Nom) | 120 V | EAN/UPC - Case | 50046677168259 |
| Mechanical and Housing | | | |
| Bulb Finish | Clear | | |

DuraMax Deco Blunt Tip

Dimensional drawing

Product

BC40B10-1/2C/CL/LL 120V 6/2TP

