



# Deco Tubular

## 15W E14 220-240V T25 CL 2BC/5

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base


### Product data

General Information	
Cap base	E14 [ E14]
Burning Position	UNIVERSAL [ Any/Universal]
Nominal lifetime (nom.)	1000 h
Light Technical	
Lamp Luminous Flux 25°C EL (Nom)	100 lm
Operating and Electrical	
Power (Rated) (Nom)	15 W
Starting time (nom.)	0.0 s
Voltage (Nom)	230-240 V
Mechanical and Housing	
Bulb finish	Clear

Approval and Application	
Energy efficiency label (EEL)	E
Product Data	
Full product code	871016307943101
Order product name	15W E14 220-240V T25 CL 2BC/5
EAN/UPC – product	8718291225010
Order code	925350044401
Numerator – quantity per pack	1
Numerator – packs per outer box	5
Material no. (12NC)	925350044401
Net weight (piece)	0.019 kg

## Deco Tubular

### Dimensional drawing



TUB 15W E14 230-240V T25 CL

Product	D	C (max)
15W E14 220-240V T25 CL 2BC/5	25 mm	54 mm

