



Deco Tubular

15W E14 220-240V T25 CL 2BC/5

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 hour(s)
Rated Lifetime (Hours)	1,000 hour(s)
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	100 lm
Operating and Electrical	
Power Consumption	15 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	230-240 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	T25 [T 25mm]
Product Data	
Order product name	15W E14 220-240V T25 CL 2BC/5
Full product name	15W E14 220-240V T25 CL 2BC/5
Full product code	871016307943101
Order code	925350044401
Material Nr. (12NC)	925350044401
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163079431
Numerator - Packs per outer box	5
EAN/UPC - Case	8718291225010

Deco Tubular

Dimensional drawing



Product	D	C (max)
15W E14 220-240V T25 CL 2BC/5	25 mm	54 mm

