



Deco Tubular

25W E14 220-240V T25 CL OV 1BL/5

Tubular lamps with single- and coiled-coil filaments and clear, inside frosted or internally coated white bulbs with B- or E-base


Product data

General Information	
Cap-Base	E14 [E14]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	1,000 h
Rated Lifetime (Hours)	1,000 h
Lighting Technology	Incandescent
Light Technical	
Luminous Flux	172 lm
Operating and Electrical	
Power Consumption	25 W
Starting Time (Nom)	0.0 s
Voltage (Nom)	230-240 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Shape	T25 [T 25mm]
Product Data	
Order product name	25W E14 220-240V T25 CL OV 1BL/5
Full product name	25W E14 220-240V T25 CL OV 1BL/5
Full product code	871016307944801
Local code description	OVEN25W240VSES
Order code	925350344401
Material Nr. (12NC)	925350344401
Local order code	OVEN25W240VSES
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163079448
Numerator - Packs per outer box	5
EAN/UPC - Case	8718291225089

Deco Tubular

Dimensional drawing



Product	D	C (max)
25W E14 220-240V T25 CL OV 1BL/5	25 mm	54 mm

