



Lumiblade OLED Panel GL

OLED Panel Brite FL300L ww N w/o Rset

High brightness functional lighting OLED panels.

Warnings and Safety

- OLEDs must be used in conjunction with suitable electronics that disconnect the OLED from the power supply in case of a short circuit. Use of Short Circuit Protection required.

Product data

Light Technical	
Luminous Flux	300 lumen
Life to 70% Lumen Maintenance	10,000 hour(s)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (Rated) (Max)	50 lm/W
Luminous Efficacy (Rated) (Min)	40 lm/W
Color rendering index (CRI)	80

Operating and Electrical	
Input Voltage	20.0 V
Power Consumption	7.4 W
Lamp Current (Nom)	368 mA


Controls and Dimming	
Dimmable	Yes

Approval and Application	
Approval Marks	CE marking RoHS compliance

Product Data	
Full product code	871869653242300
Order product name	OLED Panel Brite FL300L ww N w/o Rset
Order code	925400013201
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	20
Material Nr. (12NC)	925400013201
Full product name	OLED Panel Brite FL300L ww N w/o Rset
EAN/UPC - Case	8718696532430
EAN/UPC - Product/Case	8718696532423

Lumiblade OLED Panel GL

Dimensional drawing



Product	C1	A1	A3	B1	B3
OLED Panel Brite FL300L ww N w/o Rset	1.1 mm	240.6 mm	222.0 mm	62.7 mm	46.0 mm

