



Plusline Small

PLUS PRO S 500W R7s 230V 1CT/50

Mains-voltage linear lamp giving white halogen light

Product data

General Information	
Cap-Base	R7s
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	9,900 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	19.8 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	500.0 W
Lamp Current (Nom)	2.17 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T11
Product Data	
Order product name	PLUS PRO S 500W R7s 230V 1CT/50
Full product name	PLUS PRO S 500W R7s 230V 1CT/50
Full product code	871829114776300
Order code	925632544211
Material Nr. (12NC)	925632544211
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291147763
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291147770

Plusline Small

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
PLUS PRO S 500W R7s 230V 1CT/50	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm

