



Essential MV Capsule

ESS Capsule 40W G9 240V FR 2BC/12

The Essential MV Capsule is part of the Philips "Value for Money" ranges. As an alternative to Essential Capsule, it is ideal for professional end-users who want to have sparkling light - with easy Installation - in hotels and restaurants.


Product data

General Information	
Cap-Base	G9 [G9]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen
Light Technical	
Luminous Flux	460 lm
Luminous Efficacy (rated) (Nom)	11.5 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	40 W
Voltage (Nom)	240 V
Voltage (Nom)	240 V
Mechanical and Housing	
Bulb Finish	Frosted

Bulb Shape	T13 [T 13 mm]
Product Data	
Order product name	ESS Capsule 40W G9 240V FR 2BC/12
Full product name	ESS Capsule 40W G9 240V FR 2BC/12
Full product code	872790082203801
Local code description	G940W240VFRB2
Order code	925635945504
Material Nr. (12NC)	925635945504
Local order code	G940W240VFRB2
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900822038
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291224556

Essential MV Capsule

Dimensional drawing



Product	D (max)	C (max)
ESS Capsule 40W G9 240V FR 2BC/12	12.75 mm	44.6 mm

