



# Halogen Classic Reflector

## EcoClassic 42W E27 230V NR63 FR 1CT/10

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen

  

Light Technical	
Beam Angle (Nom)	30 degree(s)
Correlated Color Temperature (Nom)	2800 K
Color rendering index (CRI)	100
Luminous Flux in 90° Cone (Rated)	270 lm

  

Operating and Electrical	
Power Consumption	42.0 W
Lamp Current (Nom)	0.18 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes

  

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	NR63 [NR 63mm]

  

Approval and Application	
Energy Consumption kWh/1000 h	42 kWh

  

Product Data	
Order product name	EcoClassic 42W E27 230V NR63 FR 1CT/10
Full product name	EcoClassic 42W E27 230V NR63 FR 1CT/10
Full product code	872790025195125
Order code	925636044201
Material Nr. (12NC)	925636044201
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900251951
Numerator - Packs per outer box	10
EAN/UPC - Case	8727900660777

# Halogen Classic Reflector

## Dimensional drawing

Product	D (max)	C (max)
EcoClassic 42W E27 230V NR63 FR 1CT/10	64 mm	104 mm

