



# Halogen Classic Candle B35

## ClassicHalogen28W E14 240V B35 CL 1CT/15

Philips Halogen Classic Candle light bulbs offer the classical shape you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.

### Product data

General Information	
Cap base	E14 [ E14]
Operating position	UNIVERSAL [ Any or Universal (U)]
Nominal lifetime (nom.)	2000 h
Switching cycle	8000X

Light Technical	
Luminous flux (nom.)	370 lm
Luminous flux (rated) (nom.)	370 lm
Correlated Colour Temperature (Nom)	2800 K
Luminous efficacy (rated) (nom.)	12.4 lm/W
Color rendering index (nom.)	100
LLMF at end of nominal lifetime (min.)	80 %

Operating and Electrical	
Power (Rated) (Nom)	28.0 W
Lamp current (nom.)	0.12 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light (nom.)	instant full light
Power factor (nom.)	1
Voltage (Nom)	240 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb finish	Clear

Approval and Application	
Energy efficiency label (EEL)	D
Energy Consumption kWh/1000 h	28 kWh

Luminaire Design Requirements	
Cap base temperature (max.)	130 °C

Product Data	
Full product code	871829112275300
Order product name	ClassicHalogen28W E14 240V B35 CL 1CT/15
EAN/UPC – product	8718291122753
Order code	12275300
Numerator – quantity per pack	1
Numerator – packs per outer box	15
Material no. (12NC)	925639645503
Net weight (piece)	18.400 g

# Halogen Classic Candle B35

---

## Dimensional drawing



Product	D (max)	C (max)
ClassicHalogen28W E14 240V B35 CL 1CT/15	36 mm	99.2 mm

HalClass 28W E14 240V B35 CL

