



# Halogen Clickline G9

## Halogen MV Click 28W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

### Product data

| General Information        |                                  |
|----------------------------|----------------------------------|
| Cap-Base                   | G9 [G9]                          |
| Operating Position         | UNIVERSAL [Any or Universal (U)] |
| Nominal lifetime           | 2,000 hour(s)                    |
| Switching Cycle            | 8,000                            |
| Rated Lifetime (Hours)     | 2,000 hour(s)                    |
| Lighting Technology        | Halogen                          |
| Flux measurement reference | Sphere                           |

| Light Technical                    |           |
|------------------------------------|-----------|
| Luminous Flux                      | 350 lm    |
| Chromaticity Coordinate X (Nom)    | 0.452     |
| Chromaticity Coordinate Y (Nom)    | 0.409     |
| Correlated Color Temperature (Nom) | 2800 K    |
| Luminous Efficacy (rated) (Nom)    | 12.1 lm/W |
| Color rendering index (CRI)        | 100       |

| Operating and Electrical  |                      |
|---------------------------|----------------------|
| Power Consumption         | 29 W                 |
| Lamp Current (Nom)        | 0.12 A               |
| Starting Time (Nom)       | 0.0 s                |
| Warm-up time to 60% light | instant full light s |
| Power Factor (Fraction)   | 1                    |
| Voltage (Nom)             | 230 V                |

|               |       |
|---------------|-------|
| Voltage (Nom) | 230 V |
|---------------|-------|

| Controls and Dimming |     |
|----------------------|-----|
| Dimmable             | Yes |


| Mechanical and Housing |               |
|------------------------|---------------|
| Bulb Finish            | Clear         |
| Bulb Shape             | T13 [T 13 mm] |

| Approval and Application      |        |
|-------------------------------|--------|
| Energy Efficiency Class       | G      |
| Energy Consumption kWh/1000 h | 29 kWh |
| EPREL Registration Number     | 423233 |

| Product Data                    |                                     |
|---------------------------------|-------------------------------------|
| Order product name              | Halogen MV Click 28W G9 230V CL 1CT |
| Full product name               | Halogen MV Click 28W G9 230V CL 1CT |
| Full product code               | 872790086398700                     |
| Order code                      | 86398700                            |
| Material Nr. (12NC)             | 925640644205                        |
| Numerator - Quantity Per Pack   | 1                                   |
| EAN/UPC - Product/Case          | 8727900863987                       |
| Numerator - Packs per outer box | 100                                 |
| EAN/UPC - Case                  | 8727900864007                       |

# Halogen Clickline G9

## Dimensional drawing



| Product                             | D (max) | L       | C (max) |
|-------------------------------------|---------|---------|---------|
| Halogen MV Click 28W G9 230V CL 1CT | 13 mm   | 21.7 mm | 45 mm   |

