



Halogen Clickline G9

Halogen MV Click 28W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.


Product data

General Information	
Cap-Base	G9 [G9]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal Lifetime (Nom)	2000 h
Switching Cycle	8000X
Light Technical	
Luminous Flux (Nom)	370 lm
Luminous Flux (Rated) (Nom)	370 lm
Colour Temperature, horizontal (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	12.1 lm/W
Colour Rendering Index horiz (Nom)	100
LLMF at End of Nominal Lifetime (Min)	80 %
Operating and Electrical	
Power (Rated) (Nom)	28.0 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm Up Time to 60% Light (Nom)	instant full light
Power Factor (Nom)	1
Voltage (Nom)	230 V
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label	D
Energy Consumption kWh/1000 h	28 kWh
Luminaire Design Requirements	
Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	350 °C
Product Data	
Full product code	872790086398700
Order product name	Halogen MV Click 28W G9 230V CL 1CT
EAN/UPC - Product	8727900863987
Order code	86398700
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	100
Material Nr. (12NC)	925640644205
Net Weight (Piece)	0.003 kg

Halogen Clickline G9

Dimensional drawing



CLICKLINE 28W G9 230V CL

Product	D (max)	L	C (max)
Halogen MV Click 28W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

