



# Halogen Clickline G9



## Halogen MV Click 28W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

### Product data

General Information	
Cap-Base	G9
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Flux measurement reference	Sphere

Light Technical	
Luminous Flux	350 lm
Chromaticity Coordinate X (Nom)	0.452
Chromaticity Coordinate Y (Nom)	0.409
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	12.1 lm/W
Color rendering index (CRI)	100

Operating and Electrical	
Power Consumption	29 W
Lamp Current (Nom)	0.12 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V

Voltage (Nom)	230 V
---------------	-------

Controls and Dimming	
Dimmable	Yes


Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T13

Approval and Application	
Energy Efficiency Class	G
Energy Consumption kWh/1000 h	29 kWh
EPREL Registration Number	423233

Product Data	
Order product name	Halogen MV Click 28W G9 230V CL 1CT
Full product name	Halogen MV Click 28W G9 230V CL 1CT
Full product code	872790086398700
Order code	86398700
Material Nr. (12NC)	925640644205
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900863987
Numerator - Packs per outer box	100
EAN/UPC - Case	8727900864007

# Halogen Clickline G9

## Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Click 28W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

