



# Halogen Clickline G9

## Halogen Capsule 28W G9 240V 1BC/15 SRP

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime.

### Product data

General Information	
Cap base	G9 [G9]
Operating position	UNIVERSAL [Any or Universal (U)]
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen

Light Technical	
Luminous Flux	370 lm
Correlated Colour Temperature	2800 K
Luminous efficacy (rated) (nom.)	12.1 lm/W
Colour rendering index (CRI)	100

Operating and Electrical	
Power Consumption	28 W
Lamp current (nom.)	0.12 A
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	240 V
Voltage (nom.)	240 V


Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T13 [T 13 mm]

Product Data	
Order product name	Halogen Capsule 28W G9 240V 1BC/15 SRP
Full product name	Halogen Capsule 28W G9 240V 1BC/15 SRP
Full EOC	872790025289701
Order code	25289701
Material no. (12 NC)	925640645506
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900252897
Numerator – packs per outer box	15
EAN/UPC – Case	8718291229476

# Halogen Clickline G9

## Dimensional drawing



Product	D (max)	L	C (max)
Halogen Capsule 28W G9 240V 1BC/15 SRP	12.75 mm	21.7 mm	44.6 mm

