



Halogen Clickline G9



Halogen MV Click 42W G9 230V CL 1CT

Ideal solution for small decorative luminaires. UV-block glass and safety fuse allow usage without cover glass. The compact Clickline gives crisp white light over a long lifetime

Product data


General Information			
Cap-Base	G9 [G9]		
Operating Position	UNIVERSAL [Any or Universal (U)]		
Nominal lifetime	2,000 hour(s)		
Switching Cycle	8,000		
Rated Lifetime (Hours)	2,000 hour(s)		
Lighting Technology	Halogen		
Flux measurement reference	Sphere		
Light Technical			
Luminous Flux	590 lm		
Chromaticity Coordinate X (Nom)	0.452		
Chromaticity Coordinate Y (Nom)	0.409		
Correlated Color Temperature (Nom)	2800 K		
Luminous Efficacy (rated) (Nom)	15 lm/W		
Color rendering index (CRI)	100		
Operating and Electrical			
Power Consumption	44 W		
Lamp Current (Nom)	0.18 A		
Starting Time (Nom)	0.0 s		
Warm-up time to 60% light	instant full light s		
Power Factor (Fraction)	1		
Voltage (Nom)	230 V		

Voltage (Nom)	230 V		
Controls and Dimming			
Dimmable	Yes		
Mechanical and Housing			
Bulb Finish	Clear		
Bulb Shape	T13 [T 13 mm]		
Approval and Application			
Energy Efficiency Class	G		
Energy Consumption kWh/1000 h	44 kWh		
EPREL Registration Number	423238		
Product Data			
Order product name	Halogen MV Click 42W G9 230V CL 1CT		
Full product name	Halogen MV Click 42W G9 230V CL 1CT		
Full product code	872790086401400		
Order code	86401400		
Material Nr. (12NC)	925640844205		
Numerator - Quantity Per Pack	1		
EAN/UPC - Product/Case	8727900864014		
Numerator - Packs per outer box	100		
EAN/UPC - Case	8727900864038		

Datasheet, 2023, April 29 data subject to change

Halogen Clickline G9

Dimensional drawing



Product	D (max)	L	C (max)
Halogen MV Click 42W G9 230V CL 1CT	13 mm	21.7 mm	45 mm

