



Essential MV MR16 Alu

ESS MR16 Alu 50W GU10 230V 36D 1CT

The Essential MV MR16 Alu is part of the Philips "Value for Money" ranges. It is ideal for professional end-users looking for accent light - without a transformer - to create contrast in shops, hotels and restaurants.

Product data


General Information		
Cap-Base	GU10 [GU10]	
Operating Position	UNIVERSAL [Any or Universal (U)]	
Nominal lifetime	2,000 hour(s)	
Switching Cycle	8,000	
Rated Lifetime (Hours)	2,000 hour(s)	
Lighting Technology	Halogen	
Light Technical		
Beam Angle (Nom)	36 degree(s)	
Correlated Color Temperature (Nom)	2800 K	
Color rendering index (CRI)	100	
Operating and Electrical		
Power Consumption	50 W	
Starting Time (Nom)	0.0 s	
Voltage (Nom)	230 V	
Voltage (Nom)	230 V	

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	MR16 [2inch/50mm]
Product Data	
Order product name	ESS MR16 Alu 50W GU10 230V 36D 1CT
Full product name	ESS MR16 Alu 50W GU10 230V 36D 1CT
Full product code	871829119517700
Order code	925644344203
Material Nr. (12NC)	925644344203
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291195177
Numerator - Packs per outer box	50
EAN/UPC - Case	8718291195191

Datasheet, 2023, April 15 data subject to change

Essential MV MR16 Alu

Dimensional drawing



Product	D (max)	C (max)
ESS MR16 Alu 50W GU10 230V 36D 1CT	51 mm	51 mm



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.