



Halogen Classic P45

EcoClassic 42W E27 230V P45 CL 1CT/15

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.


Product data

General Information	
Cap-Base	E27 [E27]
Operating Position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 hour(s)
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 hour(s)
Lighting Technology	Halogen
Light Technical	
Luminous Flux	630 lm
Correlated Color Temperature (Nom)	2800 K
Luminous Efficacy (rated) (Nom)	15.0 lm/W
Color rendering index (CRI)	100
Operating and Electrical	
Power Consumption	42.0 W
Lamp Current (Nom)	0.18 A
Starting Time (Nom)	0.0 s
Warm-up time to 60% light	instant full light s
Power Factor (Fraction)	1
Voltage (Nom)	230 V
Voltage (Nom)	230 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	P45 [P 45mm]
Approval and Application	
Energy Consumption kWh/1000 h	42 kWh
Product Data	
Order product name	EcoClassic 42W E27 230V P45 CL 1CT/15
Full product name	EcoClassic 42W E27 230V P45 CL 1CT/15
Full product code	871869646634600
Order code	925647544224
Material Nr. (12NC)	925647544224
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696466346
Numerator - Packs per outer box	15
EAN/UPC - Case	8718696466353

Halogen Classic P45

Dimensional drawing



Product	D (max)	C (max)
EcoClassic 42W E27 230V P45 CL 1CT/15	46 mm	74 mm

