



Halogen Classic P45

Halogen Classic 28W E14 240V P45 1CT/15 SRP

Philips Halogen Classic light bulbs offer the classical shapes you are used to. This new 'classic' gives high-quality light, is dimmable and starts immediately.


Product data

General Information	
Cap base	E14 [E14]
Operating position	UNIVERSAL [Any or Universal (U)]
Nominal lifetime	2,000 h
Switching Cycle	8,000
Rated Lifetime (Hours)	2,000 h
Lighting Technology	Halogen
Light Technical	
Luminous Flux	370 lm
Correlated Colour Temperature	2800 K
Luminous efficacy (rated) (nom.)	12.4 lm/W
Colour rendering index (CRI)	100
Operating and Electrical	
Power Consumption	28.0 W
Lamp current (nom.)	0.12 A
Starting time (nom.)	0.0 s
Warm-up time to 60% light	Instant full light s
Power Factor (Fraction)	1
Voltage (nom.)	240 V
Voltage (nom.)	240 V

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	P45 [P 45 mm]
Approval and Application	
Energy consumption kWh/1,000 hours	28 kWh
Product Data	
Order product name	Halogen 28W E14 240V P45 1CT/15 SRP
Full product name	Halogen Classic 28W E14 240V P45 1CT/15 SRP
Full EOC	872790083579304
Order code	83579304
Material no. (12 NC)	925648345505
Local order code	28SESECOCLASP45
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8727900835793
Numerator – packs per outer box	15
EAN/UPC – Case	8718696462560

Halogen Classic P45

Dimensional drawing



Product	D (max)	C (max)
Halogen 28W E14 240V P45 1CT/15 SRP	46 mm	80 mm

